

L-Cube Tall cabinet # LC1170 L/R

| < 15 3/4" Inch > |



Tall cabinet	Dimension	Weight	Order number
1 door, 4 glass shelves with Aluminum brackets			
Colors			
M03 Jade High Gloss Lacquer M07 Concrete Gray Matt Decor M09 Light Blue Matt Decor M10 Apricot Pearl High Gloss Lacquer M11 Cashmere Oak M12 Brushed Oak (Real wood veneer) M13 American Walnut (Real wood veneer) M18 White Matt M20 Apricot Pearl Satin Matt Lacquer M21 Walnut Dark Decor M22 White High Gloss (Decor) M27 White Lilac High Gloss Lacquer M31 Pine Silver (Decor) M38 Dolomiti Gray High Gloss Lacquer M40 Black High Gloss Lacquer M43 Basalt Matt (Decor) M47 Stone Blue High Gloss Lacquer M49 Graphite Matt (Decor) M51 Pine Terra (Decor) M52 European Oak (Decor) M53 Chestnut Dark (Decor) M61 Olive Brown High Gloss Lacquer M69 Brushed Walnut (Real wood veneer) M71 Mediterranean Oak (Real wood veneer) M72 Brushed Dark Oak (Real wood veneer) M73 Ticino Cherry Tree (Decor) M75 Linen (Decor) M79 Natural Walnut (Decor) M85 White High Gloss Lacquer M86 Cappuccino High Gloss Lacquer M87 White Lilac Satin Matt Lacquer M89 Flannel Gray High Gloss Lacquer M90 Flannel Grey Satin Matt Lacquer M91 Taupe Matt (Decor)			
Variant			
	15 3/4" x 9 1/2" Inch		LC1170 L/R
Infobox			
Please keep a minimum distance of 2" to the wall, If adjacent to furniture, a space of 2" is necessary, Legs are available as an option, # UV 9991 (Aluminum Matt) consists of 2 pieces. If 4 pieces are desired, please order 2x # UV 9991, # UV 9993 (Chrome) consists of 2 pieces. If 4 pieces are desired, please order 2 x # UV 9993, Legs # UV 9992 and UV 9994 are not suitable, Required specification for ordering: - Hinges left (L) or right (R)			
Suitable products			
Legs Aluminum Matt, 2 pieces, 5 7/8" x 1 3/4" x 3/8" Inch	5 7/8" x 1 3/4" x 3/8" Inch		UV9991
Legs Chrome, 2 pieces, 5 7/8" x 1 3/4" x 3/8" Inch	5 7/8" x 1 3/4" x 3/8" Inch		UV9993

All drawings contain the necessary measurements which are subject to standard tolerances. They are stated in inch & mm and are non-binding. Exact measurements, in particular for customized installation scenarios, can only be taken from the finished ceramic piece.