

BC 05 - no apron

inch 72x40x24 mm 1829x1016x610

■ interior dimensions

rim: inch 58x26 mm 1473x660 base: inch 48x25 mm 1219x635 height: inch 20 mm 508

■ capacity to overflow gal (us) - 82 liters- 310

■ weight

lb - 220 kg - 100

■ installation

drop-in bathtub (BC 0501) 1 wall, 2 walls or 3 walls

accessory

oak bridge wenge shade


■ material


WETMAR BiO™, True High Gloss™ or matte finish

■ color white

■ codes/standards applicable IAPMO-ANSI Z124.1 IAPMO-ANSI Z124.3 CSA B 45.0 – CSA B45.4










WETSTYLE Plug & Bathe™ overflow and drain connection system includes:

Soft-touch pop-up drain, for built-in overflow. Fits both 1-1/2" ABS drain waste and 1-1/2" tubular brass

1-1/2" ABS Direct vertical drain waste fitting (copper/brass option also available)

1-1/2" ABS 90° Elbow drain waste fitting (copper/brass option also available)



WETSTYLE cannot be held responsible for any technical errors and reserves the right to make revisions without notice.

Approximate measurement.
The manufacturer accept ¼" (6.35mm) variance.

www.**WETSTYLE.CA** - Montreal - Canada Tel. **450.536.9000** - 1 888.536.9001 - Fax. 450.536.0202





inch 72x40x24 mm 1829x1016x610

■ overflow and drain connection WETSTYLE Plug & Bathe™ system (ABS or copper/brass)

■ overflow

slot design polished chrome or brushed nickel

■ drain

soft toe touch polished chrome or brushed nickel

■ waste and overflow kit included


■ faucet area recommended bath deck


or floor-mounted

■ trap access

white access panel

wide-deck bathtub; wall shower installation is <u>not</u> recommended





Bathtub installation supplies

A tile flange will be supplied to comply with the requested position. Installed at the factory to prevent water leakage, this must be placed directly on the partition framing prior to the installation of drywall.

WETSTYLE cannot be held responsible for any technical errors and reserves the right to make revisions without notice.

Approximate measurement.

The manufacturer accept ¼" (6.35mm) variance.

